



### Outline Dimensions



### PCB Land Pattern



Suggested Layout,  
Tolerance to be within  $\pm.002$

CASE #	A	B	C	D	E	F	G	H	J	K	L	M
FV1206-6	.126 (3.20)	.063 (1.60)	.037 (0.95)	.013 (0.33)	.022 (0.56)	.012 (0.30)	.039 (0.99)	.026 (0.65)	.041 (1.05)	.119 (3.02)	.020 (0.50)	.174 (4.42)

CASE #	N	P	Q	R	S	WT. GRAM
FV1206-6	.014 (0.35)	-- --	.012 (0.30)	.039 (0.99)	.096 (2.44)	.017

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm.01$ ; 3 Pl.  $\pm.005$

#### Notes:

1. Open style, ceramic base.
2. Termination finish: **as shown below or indicated on Data Sheet.**  
For RoHS Case Styles: Tin plate over Nickel Plate. All models, (+) suffix.