


Outline Dimensions

HW1388



* OVERALL CONNECTOR OR CABLE & BOOT DIMENSION
(CONNECTOR SHAPE MAY VARY)

HW1388 SERIES

N MALE (CONN-1)

N MALE (CONN-2)

CASE STYLE #	A		B	C	D	E	T		WEIGHT GRAMS
	FEET	METERS					FEET	METERS	
HW1388-1	1	.30	.88 (22.35)	.750 (19.05)	.88 (22.35)	.750 (19.05)	.06	.02	174
HW1388-2	2	.61					.06	.02	250
HW1388-3	3	.91					.09	.03	326
HW1388-3.28	3.28	1.00					.10	.03	347
HW1388-4	4	1.22					.12	.04	402
HW1388-4.92	4.92	1.50					.15	.05	472
HW1388-5	5	1.52					.15	.05	479
HW1388-6	6	1.83					.18	.05	555
HW1388-6.56	6.56	2.00					.20	.06	597
HW1388-7	7	2.13					.21	.06	631
HW1388-8	8	2.44					.24	.07	707
HW1388-9	9	2.74					.27	.08	783
HW1388-9.84	9.84	3.00					.30	.09	847
HW1388-10	10	3.05					.30	.09	860
HW1388-11	11	3.35					.33	.10	936
HW1388-12	12	3.66					.36	.11	1012
HW1388-13	13	3.96					.39	.12	1088
HW1388-14	14	4.27					.42	.13	1164
HW1388-15	15	4.57					.45	.14	1241
HW1388-16	16	4.88					.48	.15	1317
HW1388-16.4	16.4	5.00	.49	.15	1347				
HW1388-17	17	5.18	.51	.16	1393				
HW1388-18	18	5.49	.54	.16	1469				
HW1388-19	19	5.79	.57	.17	1545				
HW1388-20	20	6.10	.60	.18	1622				
HW1388-32.8	32.81	10.00	.98	.30	2598				
HW1388-49.2	49.21	15.00	1.48	.45	3847				
HW1388-125	125	38.10	3.75	1.14	9623				
HW1388-131	131.23	40.00	3.94	1.20	10097				

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. ± .03; 3Pl. ± .015

Note:

1. Flexible Coaxial Cable.



INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified