


### Outline Dimensions



\* OVERALL CONNECTOR DIMENSION  
(CONNECTOR SHAPE MAY VARY)

CUT OUT FOR SMA FEMALE BULKHEAD CONNECTOR  
PANEL THICKNESS .100 MAX INCHES

KP1567 SERIES  
SMA FEMALE BULKHEAD (CONN-1)  
SMA MALE (CONN-2)

| CASE STYLE # | A     |        | B              | C1              | C2             | D             | E1             | E2             | F   |                        | T    |      | WEIGHT GRAMS |
|--------------|-------|--------|----------------|-----------------|----------------|---------------|----------------|----------------|---|------------------------|------|------|--------------|
|              | INCH  | MM     |                |                 |                |               |                |                | 086U-ASM+                                 | 086-ASM+               | INCH | MM   |              |
| KP1567-3     | 3.00  | 76.20  | .51<br>(12.95) | .438<br>(11.13) | .232<br>(5.89) | .36<br>(9.14) | .313<br>(7.95) | .250<br>(6.35) | .089 $\nabla$ .002<br>(2.26 $\nabla$ .06) | .108 NOM<br>(2.75 NOM) | .05  | 1.27 | 7.37         |
| KP1567-5     | 5.00  | 127.00 |                |                 |                |               |                |                |   |                        | .05  | 1.27 | 8.29         |
| KP1567-6     | 6.00  | 152.40 |                |                 |                |               |                |                |   |                        | .05  | 1.27 | 8.74         |
| KP1567-7     | 7.00  | 177.80 |                |                 |                |               |                |                |   |                        | .10  | 2.54 | 9.20         |
| KP1567-8     | 8.00  | 203.20 |                |                 |                |               |                |                |   |                        | .10  | 2.54 | 9.66         |
| KP1567-9     | 9.00  | 228.60 |                |                 |                |               |                |                |   |                        | .10  | 2.54 | 10.11        |
| KP1567-10    | 10.00 | 254.00 |                |                 |                |               |                |                |   |                        | .10  | 2.54 | 10.57        |
| KP1567-11    | 11.00 | 279.40 |                |                 |                |               |                |                |   |                        | .10  | 2.54 | 11.03        |
| KP1567-12    | 12.00 | 304.80 |                |                 |                |               |                |                |   |                        | .10  | 2.54 | 11.48        |
| KP1567-13    | 13.00 | 330.20 |                |                 |                |               |                |                |   |                        | .15  | 3.81 | 11.94        |
| KP1567-14    | 14.00 | 355.60 |                |                 |                |               |                |                |   |                        | .15  | 3.81 | 12.40        |
| KP1567-16    | 16.00 | 406.40 |                |                 |                |               |                |                |   |                        | .15  | 3.81 | 13.31        |

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl.  $\pm$  .03; 3Pl.  $\pm$  .015

#### Note:

1. 086 Hand-Flex™ Coaxial Cable.
2. "A" represents length of cable.