


Outline Dimensions



* OVERALL CONNECTOR DIMENSION
(CONNECTOR SHAPE MAY VARY)

MU1838 SERIES
SMA MALE (CONN-1)
SMA MALE (CONN-2)

CASE STYLE #	A		B	C	D	E	F	T		WEIGHT GRAMS
	FEET	METERS						INCH	MM	
MU1838-1	1.00	0.30	.42 (10.70)	.312 (7.93)	.42 (10.70)	.312 (7.93)	.194 (4.95)	+.50/-0	+12.7/-0	41
MU1838-1.5	1.50	0.46						+.50/-0	+12.7/-0	47
MU1838-2	2.00	0.61						+.50/-0	+12.7/-0	56
MU1838-3	3.00	0.91						+.72/-0	+18.3/-0	72
MU1838-3.28	3.28	1.00						+.79/-0	+20.0/-0	77
MU1838-4	4.00	1.22						+.96/-0	+24.4/-0	89
MU1838-6	6.00	1.83						+1.44/-0	+36.6/-0	123
MU1838-6.56	6.56	2.00						+1.57/-0	+40.0/-0	132

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. ± .03; 3Pl. ± .015

Note:

1. Flexible Low Loss Cable.