


### Outline Dimensions



\* OVERALL CONNECTOR DIMENSION  
(CONNECTOR SHAPE MAY VARY)

MU2339 SERIES  
SMA MALE (CONN-1)  
N MALE (CONN-2)

CASE STYLE #	A		B	C	D	E	F	T		WEIGHT GRAMS			
	FEET	METERS						INCH	MM				
MU2339-6.56	6.56	2.00	.42 (10.70)	.312 (7.93)	.84 (21.3)	.75 (19.0)	.194 (4.95)	+1.57/-0	+40.0/-0	156			

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2Pl. ± .03; 3Pl. ± .015

Note:

1. Flexible Low Loss Cable.