


Outline Dimensions

UL3033



UL3030 SERIES

2.92 MM MALE (CONN 1)

2.4 MM MALE (CONN 2)

CASE STYLE #	A		B	C1	D	E1	F		T		WT. (GRAMS)
	INCH	MM					FL47U- AKMVM+ (UN-JACKETED)	FL47- AKMVM+ (JACKETED)	INCH	MM	
UL3033-6	6.00	152.40	.36 [9.14]	.315 [8.00]	.36 [9.14]	.315 [8.00]	.046±.004 [1.17±0.1]	.055±.004 [1.40±0.1]	.05	1.27	9.44
UL3033-12	12.00	304.80							.10	2.54	10.28

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2 Pl.± .03; 3 Pl. ± .015

Note:

- 047 Flexible Coaxial Cable
- "A" Represents Length of cable.

Mini-Circuits®

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

Mini-Circuits ISO 9001 & ISO 14001 Certified