



UL3034 SERIES
 SSMP FEMALE (CONN 1)
 2.92 MM MALE (CONN 2)

CASE STYLE #	A		B	C1	C2	D	E1	E2	F		T		WT. (GRAMS)
	INCH	MM							FL47U-ASSMPKM+ (UN-JACKETED)	FL47-ASSMPKM+ (JACKETED)	INCH	MM	
UL3034-6	6.00	157.40									.05	1.27	5.49
UL3034-12	12.00	304.80	.14	.093	.303	.36	.315	-	.046±.004	.055±.004	.10	2.54	6.33
			[3.56]	[2.36]	[7.70]	[9.14]	[8.00]	-	[1.17±0.1]	[1.40±0.1]			

Unless otherwise specified dimensions are in inches (mm).

Tolerances: 2 Pl.±.03; 3 Pl. ±.015

Note:

- 047 Flexible Coaxial Cable.
- "A" Represents Length of Cable.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: www.minicircuits.com

RF/IF MICROWAVE COMPONENTS