


## Outline Dimensions

UU2372-1



CASE#	A	B	C	D	E	F	G	H	J	K	L	M
UU2372-1	4.25 (108.0)	9.50 (241.30)	.50 (12.70)	.15 (3.81)	3.95 (100.33)	.75 (19.05)	8.000 (203.2)	.136 (3.45)	2.13 (53.98)	.205 (5.21)	.63 (15.88)	1.88 (47.63)

CASE#	N	P	Q	R	S	WT. GRAMS
UU2372-1	3.13 (79.38)	-	-	-	.500 (12.70)	600

Dimensions are in inches (mm). Tolerances: 2 Pl.  $\pm .03$ ; 3 Pl.  $\pm .015$

### Notes:

1. Case material: Aluminum alloy.
2. Case finish:  
For RoHS Case Styles: Clear chemical conversion coating, non-chrome or trivalent chrome based.
3. Refer to the individual model data sheet for the type of connectors available.



P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661 For detailed performance specs & shopping online see Mini-Circuits web site



The Design Engineers Search Engine Provides ACTUAL Data Instantly From MINI-CIRCUITS At: [www.minicircuits.com](http://www.minicircuits.com)

RF/IF MICROWAVE COMPONENTS