

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.92mm-MALE 1 RETURN LOSS (dB)	2.92mm-MALE 2 RETURN LOSS (dB)
10	0.04	52.7	46.9
50	0.04	43.1	41.6
100	0.06	39.5	39.2
1000	0.22	48.3	48.6
2000	0.33	48.1	49.3
3000	0.41	28.6	28.5
4000	0.48	34.9	35.0
5000	0.53	35.3	38.9
6000	0.58	35.4	36.4
7000	0.64	24.9	25.0
8000	0.67	30.3	30.9
9000	0.72	27.2	27.5
10000	0.76	29.7	30.6
11000	0.80	34.1	34.0
12000	0.84	38.2	41.6
13000	0.88	29.6	30.1
14000	0.91	36.5	34.5
15000	0.95	35.5	35.2
16000	1.00	35.1	35.9
17000	1.03	33.8	32.7
18000	1.08	28.1	28.9
19000	1.12	29.3	32.2
20000	1.16	31.8	40.4
21000	1.20	29.6	32.3
22000	1.24	28.5	30.5
23000	1.28	26.3	34.6
24000	1.33	25.5	27.7
25000	1.36	26.7	29.9
26000	1.40	29.6	34.5
27000	1.45	25.6	26.7
28000	1.49	28.3	32.4
29000	1.52	27.5	29.8
30000	1.56	24.1	25.2
31000	1.60	26.0	27.3
32000	1.62	28.6	33.4
33000	1.67	22.6	24.2
34000	1.71	26.1	26.8
35000	1.74	29.2	34.2
36000	1.78	25.6	27.6
37000	1.83	23.2	24.2
38000	1.85	25.0	28.2
39000	1.89	24.4	26.0
40000	1.93	24.8	27.1