

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.92mm-MALE 1 RETURN LOSS (dB)	2.92mm-MALE 2 RETURN LOSS (dB)
10	0.03	52.7	50.0
50	0.01	51.6	50.9
100	0.01	50.8	47.5
1000	0.08	44.4	43.9
2000	0.11	34.7	34.1
3000	0.13	38.2	38.5
4000	0.15	33.5	33.3
5000	0.17	30.6	30.3
6000	0.17	39.8	39.2
7000	0.19	27.4	27.1
8000	0.18	50.9	48.8
9000	0.20	27.9	27.9
10000	0.20	36.8	37.0
11000	0.21	29.9	30.3
12000	0.21	35.5	36.3
13000	0.22	38.9	38.1
14000	0.23	33.9	35.6
15000	0.24	51.1	39.0
16000	0.25	34.8	35.8
17000	0.26	39.6	41.2
18000	0.27	33.7	31.9
19000	0.29	44.1	37.6
20000	0.30	42.7	33.1
21000	0.31	48.9	50.9
22000	0.33	38.0	33.1
23000	0.34	42.3	48.5
24000	0.36	33.9	33.1
25000	0.37	38.8	41.2
26000	0.39	35.7	36.3
27000	0.40	33.8	33.2
28000	0.42	34.3	32.8
29000	0.43	31.9	31.2
30000	0.44	30.1	29.2
31000	0.45	30.6	29.2
32000	0.46	26.3	26.5
33000	0.46	35.6	31.6
34000	0.49	25.6	26.3
35000	0.49	32.1	33.2
36000	0.51	25.5	25.9
37000	0.52	28.2	31.3
38000	0.53	28.5	28.1
39000	0.53	27.6	30.2
40000	0.55	32.2	31.7