

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
10.0	0.02	40.81	41.49
50.0	0.02	47.45	49.64
100.0	0.04	41.26	41.42
200.0	0.05	38.92	38.82
300.0	0.06	44.94	44.64
400.0	0.07	46.67	44.34
500.0	0.09	37.96	36.52
600.0	0.10	38.28	37.10
700.0	0.10	53.84	51.79
800.0	0.11	40.45	38.95
900.0	0.12	37.33	35.89
1000.0	0.12	43.45	42.05
1100.0	0.13	45.05	44.94
1250.0	0.14	37.22	37.22
1500.0	0.16	38.40	38.23
1750.0	0.17	51.29	48.97
2000.0	0.19	39.37	38.00
2001.0	0.19	39.45	38.05
2250.0	0.20	40.34	39.03
2500.0	0.21	49.16	46.12
2750.0	0.22	48.80	40.94
3000.0	0.24	49.50	41.75
3250.0	0.25	46.40	45.05
3500.0	0.27	43.69	42.26
3750.0	0.27	41.94	44.03
4000.0	0.28	57.57	44.67
4250.0	0.28	40.48	36.25
4500.0	0.30	36.55	34.98
5000.0	0.32	46.20	48.11
5500.0	0.36	31.50	31.58
6000.0	0.37	33.93	31.27
6500.0	0.39	34.02	39.43
7000.0	0.43	30.58	29.60
7500.0	0.42	45.86	41.76
8000.0	0.47	28.55	30.91
8500.0	0.46	35.21	33.54
9000.0	0.49	30.40	31.14
9500.0	0.50	30.68	28.81
10000.0	0.51	33.73	34.76
10500.0	0.52	26.85	28.90
11000.0	0.56	36.18	33.22
11500.0	0.56	29.11	30.48
12000.0	0.60	37.66	47.14
12500.0	0.60	33.62	36.98
13000.0	0.60	37.19	31.44
13500.0	0.61	31.82	33.08
14000.0	0.61	57.28	32.78
14500.0	0.67	28.40	28.07
15000.0	0.67	35.81	31.93
15500.0	0.70	28.99	29.19
16000.0	0.67	33.98	35.52
16500.0	0.78	31.19	33.77
17000.0	0.72	41.45	46.95
17500.0	0.78	32.19	31.32
18000.0	0.74	30.62	32.45