

Hand-Flex Coaxial Cable, SMA-M/N-M

141-24SMNM+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	N-MALE RETURN LOSS (dB)
100.0	0.08	29.9	29.8
200.0	0.10	36.4	36.0
300.0	0.13	33.3	31.8
400.0	0.14	35.0	33.7
500.0	0.16	34.8	31.6
600.0	0.16	34.6	31.4
700.0	0.17	35.8	31.3
800.0	0.17	33.0	29.4
900.0	0.17	34.3	31.7
1000.0	0.20	30.8	28.3
1200.0	0.26	32.7	27.7
1400.0	0.27	33.1	28.1
1600.0	0.28	32.8	28.2
1800.0	0.29	33.5	28.9
2000.0	0.31	37.3	30.5
2200.0	0.32	31.6	28.1
2400.0	0.35	30.3	27.4
2600.0	0.36	30.7	27.9
2800.0	0.38	31.6	28.9
3000.0	0.40	30.7	28.7
3500.0	0.44	29.7	28.6
4000.0	0.48	29.5	29.0
4500.0	0.53	31.0	30.8
5000.0	0.57	30.6	30.7
5500.0	0.60	31.2	30.2
6000.0	0.64	30.5	29.0
6500.0	0.67	28.9	27.3
7000.0	0.71	32.2	28.3
7500.0	0.73	33.3	29.8
8000.0	0.77	30.8	30.1
8500.0	0.75	28.3	28.1
9000.0	0.76	28.5	27.5
9500.0	0.78	28.0	29.0
10000.0	0.83	26.2	26.3
10500.0	0.88	26.6	25.0
11000.0	0.91	25.1	22.8
11500.0	0.94	25.3	22.6
12000.0	0.95	26.0	23.6
12500.0	0.96	26.1	23.4
13000.0	1.01	25.3	22.8
13500.0	1.02	23.8	22.1
14000.0	1.01	23.8	23.3
14500.0	1.00	24.1	24.7
15000.0	1.03	25.8	23.7
15500.0	1.02	23.5	22.2
16500.0	1.03	25.8	23.8
17000.0	1.03	25.3	23.0
17500.0	1.09	23.6	23.1
18000.0	1.14	27.0	21.6