

Hand-Flex Coaxial Cable

141-2SMR+

Right Angle SMA-Male to Right Angle SMA-Male

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE 2 RETURN LOSS (dB)
10	0.002	67.24	61.26
20	0.005	60.02	59.45
30	0.002	57.01	58.07
40	0.002	55.41	55.35
50	0.004	54.05	54.23
60	0.004	52.54	52.50
70	0.004	50.84	51.02
80	0.006	50.18	49.88
90	0.006	49.54	49.20
100	0.006	48.32	49.04
200	0.010	44.90	45.19
300	0.015	41.62	41.84
400	0.016	40.63	40.92
500	0.019	39.42	39.61
950	0.028	40.16	40.60
1950	0.040	53.63	45.64
2500	0.045	39.40	39.58
3000	0.052	33.98	34.03
3450	0.055	35.75	34.95
3950	0.058	53.80	44.64
4500	0.063	32.80	32.18
5000	0.070	30.59	30.88
5500	0.069	36.54	37.72
6000	0.073	40.61	39.44
6500	0.076	34.27	34.88
6950	0.079	39.58	43.32
7450	0.080	40.44	39.85
7950	0.083	35.85	36.95
8500	0.085	44.44	47.96
9000	0.083	36.48	34.58
9500	0.087	34.56	35.61
10000	0.083	37.70	34.29
10500	0.094	30.66	29.14
11000	0.098	31.86	29.71
11500	0.095	46.15	33.32
12000	0.099	33.67	30.87
12500	0.099	32.84	32.40
12950	0.099	43.03	32.11
13450	0.103	31.35	26.84
13950	0.098	33.61	30.58
14450	0.108	39.13	34.30
14950	0.113	26.68	24.45
15450	0.098	27.30	26.64
15950	0.116	32.78	34.14
16500	0.144	23.24	21.41
17000	0.120	23.41	21.26
17500	0.109	36.99	31.68
18000	0.139	25.82	24.33