

Hand-Flex Coaxial Cable, SMA-M/N-M

141-4SMNM+

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	N-MALE RETURN LOSS (dB)
100.0	0.02	42.4	40.2
200.0	0.02	38.9	37.3
300.0	0.03	35.5	34.1
500.0	0.03	31.4	32.3
600.0	0.04	30.8	32.2
800.0	0.04	31.8	32.8
900.0	0.04	33.7	34.1
1000.0	0.04	38.0	37.1
1200.0	0.04	44.3	43.7
1400.0	0.05	36.4	36.0
1600.0	0.04	32.2	31.5
1800.0	0.06	31.2	31.1
2000.0	0.06	32.9	31.8
2200.0	0.05	34.0	31.5
2400.0	0.06	33.1	30.9
2600.0	0.05	31.6	30.3
2800.0	0.04	31.2	31.4
3000.0	0.07	33.6	34.0
3500.0	0.06	35.3	30.7
4000.0	0.07	27.4	26.2
4500.0	0.07	38.0	36.9
5000.0	0.07	34.0	27.8
5500.0	0.08	31.6	29.0
6000.0	0.07	35.9	41.3
6500.0	0.09	43.7	31.1
7000.0	0.10	33.6	31.5
7500.0	0.12	31.4	29.6
8000.0	0.10	34.6	29.8
8500.0	0.09	28.7	28.5
9000.0	0.12	32.4	31.9
9500.0	0.16	28.2	29.5
10000.0	0.13	26.7	26.7
10500.0	0.12	27.2	32.6
11000.0	0.15	26.3	30.6
11500.0	0.18	27.6	30.1
12000.0	0.14	30.5	30.3
12500.0	0.15	29.7	27.6
13000.0	0.10	30.4	31.8
13500.0	0.14	32.7	37.0
14000.0	0.25	29.2	33.9
14500.0	0.11	25.2	27.4
15000.0	0.11	26.4	25.3
15500.0	0.19	25.0	23.2
16000.0	0.12	20.7	25.8
16500.0	0.29	24.4	25.8
17000.0	0.25	24.6	24.1
17500.0	0.26	22.0	25.0
18000.0	0.29	26.1	23.7