

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
100	0.19	37.5	38.0
200	0.27	41.4	41.9
300	0.32	41.7	42.0
400	0.38	41.2	41.8
500	0.42	40.3	42.3
600	0.46	40.6	43.5
700	0.50	41.9	43.9
800	0.54	39.9	45.0
900	0.58	43.0	46.0
1000	0.62	42.8	45.6
1100	0.64	43.0	46.1
1250	0.68	43.9	45.2
1500	0.76	45.2	44.9
1750	0.83	41.1	47.9
2000	0.90	43.8	56.0
2250	0.97	44.2	43.8
2500	1.03	41.7	38.4
2750	1.10	38.2	40.2
3000	1.17	40.8	42.3
3250	1.23	38.8	41.8
3500	1.28	37.9	40.1
3750	1.34	35.5	39.6
4000	1.36	34.6	36.5
4250	1.38	37.1	34.4
4500	1.44	34.6	32.5
5000	1.53	34.7	34.4
5500	1.66	33.5	37.2
6000	1.73	30.1	30.7
6500	1.80	36.6	35.6
7000	1.86	33.1	32.6
7500	1.92	33.1	32.9
8000	1.96	30.1	32.0
8500	2.04	31.6	31.4
9000	2.15	30.4	31.1
9500	2.20	28.1	31.5
10000	2.26	29.2	31.6
11000	2.35	33.3	36.3
12000	2.43	29.0	29.8
13000	2.57	30.4	30.9
13500	2.66	32.3	32.1
14000	2.72	29.1	29.4
14500	2.73	29.1	32.6
15000	2.84	28.1	30.5
15500	2.90	26.6	31.2
16000	3.05	23.5	33.2
16500	3.02	22.8	31.3
17000	3.14	24.7	31.4
17500	3.16	27.8	30.3
18000	3.22	26.9	37.0