

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
100	0.23	37.5	38.1
200	0.33	40.0	38.3
300	0.41	42.0	39.2
400	0.47	42.3	39.5
500	0.53	40.5	39.0
600	0.58	41.6	39.0
700	0.63	43.2	39.9
800	0.67	41.4	39.1
900	0.72	41.2	38.7
1000	0.76	41.9	38.6
1100	0.80	42.2	39.3
1250	0.86	41.4	39.2
1500	0.95	41.3	40.9
1750	1.03	46.2	43.7
2000	1.11	42.0	40.0
2250	1.18	42.3	41.8
2500	1.25	42.5	41.2
2750	1.32	42.8	41.2
3000	1.39	43.4	42.3
3250	1.46	42.0	41.8
3500	1.53	44.9	44.3
3750	1.59	42.5	42.8
4000	1.64	43.2	42.2
4250	1.71	43.9	44.4
4500	1.77	42.4	41.5
5000	1.87	41.7	41.3
5500	1.98	39.7	39.9
6000	2.08	40.1	39.8
6500	2.17	40.4	40.1
7000	2.27	40.4	39.6
7500	2.38	39.4	38.2
8000	2.46	35.8	36.5
8500	2.56	37.6	35.7
9000	2.64	34.4	32.8
9500	2.73	36.1	36.9
10000	2.81	32.8	31.7
11000	2.96	36.3	32.7
12000	3.15	34.3	32.7
13000	3.29	31.1	30.5
13500	3.35	33.3	32.2
14000	3.46	31.5	29.4
14500	3.53	33.2	31.0
15000	3.60	31.4	32.6
15500	3.67	32.2	31.8
16000	3.73	31.3	30.6
16500	3.81	31.3	32.0
17000	3.90	31.6	30.0
17500	3.94	32.7	33.7
18000	4.01	42.6	37.8