

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-MALE 1 RETURN LOSS (dB)	N-MALE 2 RETURN LOSS (dB)
10	0.01	55.32	53.98
100	0.02	40.20	40.11
300	0.05	35.81	35.87
500	0.07	40.19	39.37
1000	0.11	38.63	37.83
2000	0.16	34.25	34.81
2500	0.18	31.67	31.56
3000	0.20	31.63	31.98
3500	0.21	34.69	36.13
4000	0.22	40.78	40.68
4500	0.23	41.86	45.10
5000	0.25	33.02	33.76
5500	0.27	28.54	28.92
6000	0.28	25.55	25.60
6500	0.29	29.31	29.18
7000	0.29	34.78	33.38
7500	0.31	44.71	47.56
8000	0.32	38.47	42.86
8500	0.33	47.55	39.60
9000	0.34	31.85	31.47
9500	0.34	28.62	31.01
10000	0.32	29.12	39.25
10500	0.33	25.09	28.24
11000	0.37	22.84	22.90
11500	0.42	19.94	20.72
12000	0.42	20.66	21.22
12500	0.40	21.99	23.84
13000	0.38	30.52	32.34
13500	0.41	28.73	30.69
14000	0.45	22.08	23.62
14500	0.44	23.29	24.70
15000	0.42	25.29	26.89
15500	0.41	26.38	30.00
16000	0.41	28.30	44.63
16500	0.41	28.27	35.58
17000	0.42	31.25	29.69
17500	0.45	28.47	34.33
18000	0.50	20.92	23.27