

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RIGHT ANGLE SMA-MALE 1 RETURN LOSS (dB)	RIGHT ANGLE SMA-MALE 2 RETURN LOSS (dB)
100.0	0.04	43.9	44.2
200.0	0.05	45.0	46.7
400.0	0.08	49.6	54.8
500.0	0.09	43.7	49.7
600.0	0.11	44.6	52.1
800.0	0.13	45.6	46.3
900.0	0.14	40.7	50.8
1000.0	0.14	41.9	48.3
1100.0	0.15	49.0	43.9
1250.0	0.16	41.4	46.6
1500.0	0.17	45.4	40.5
1750.0	0.19	37.2	38.9
2000.0	0.20	46.0	48.9
2250.0	0.22	39.2	37.0
2500.0	0.23	38.4	37.4
2750.0	0.25	41.0	45.8
3000.0	0.26	36.6	33.8
3250.0	0.27	32.3	31.7
3500.0	0.28	39.3	38.9
3750.0	0.29	34.4	33.3
4000.0	0.30	31.8	29.8
4250.0	0.31	33.0	31.1
4500.0	0.32	33.5	32.7
5000.0	0.34	40.0	35.1
5500.0	0.36	33.8	32.2
6000.0	0.39	32.3	35.1
6500.0	0.42	31.7	31.3
7000.0	0.44	37.1	35.1
7500.0	0.47	31.6	27.8
8000.0	0.48	30.2	30.6
8500.0	0.47	30.3	30.5
9000.0	0.47	26.4	26.7
9500.0	0.45	47.7	35.6
10000.0	0.47	34.7	31.1
10500.0	0.50	25.9	39.3
11000.0	0.52	29.6	35.6
11500.0	0.56	30.2	29.4
12000.0	0.60	27.0	37.8
12500.0	0.62	23.6	29.7
13000.0	0.64	38.7	30.7
13500.0	0.65	29.1	25.0
14000.0	0.62	28.9	35.8
14500.0	0.62	33.7	32.7
15000.0	0.63	23.0	24.0
15500.0	0.63	24.9	25.0
16000.0	0.62	28.7	25.4
16500.0	0.67	21.7	23.2
17000.0	0.66	29.5	29.0
17500.0	0.72	22.3	24.8
18000.0	0.76	24.1	23.8