

Adapter, 2.4mm Male to 2.4mm Male

24M-24M+

Typical Performance Data

| FREQUENCY (GHz) | INSERTION LOSS (dB) | 2.4mm-MALE 1 VSWR (:1) | 2.4mm-MALE 2 VSWR (:1) |
|--------------------|------------------------|------------------------------|------------------------------|
| 0.01 | 0.00 | 1.01 | 1.01 |
| 0.05 | 0.00 | 1.00 | 1.00 |
| 0.10 | 0.00 | 1.00 | 1.00 |
| 0.50 | 0.02 | 1.01 | 1.01 |
| 1 | 0.03 | 1.02 | 1.01 |
| 5 | 0.07 | 1.02 | 1.02 |
| 10 | 0.09 | 1.01 | 1.01 |
| 12 | 0.09 | 1.01 | 1.00 |
| 14 | 0.10 | 1.00 | 1.00 |
| 16 | 0.10 | 1.01 | 1.01 |
| 18 | 0.10 | 1.03 | 1.03 |
| 20 | 0.11 | 1.05 | 1.05 |
| 22 | 0.12 | 1.08 | 1.08 |
| 24 | 0.13 | 1.07 | 1.07 |
| 26 | 0.13 | 1.05 | 1.04 |
| 28 | 0.14 | 1.02 | 1.02 |
| 30 | 0.14 | 1.02 | 1.01 |
| 32 | 0.15 | 1.00 | 1.01 |
| 34 | 0.16 | 1.02 | 1.04 |
| 36 | 0.16 | 1.01 | 1.02 |
| 38 | 0.17 | 1.03 | 1.03 |
| 40 | 0.19 | 1.07 | 1.07 |
| 42 | 0.20 | 1.10 | 1.09 |
| 44 | 0.19 | 1.07 | 1.07 |
| 46 | 0.21 | 1.05 | 1.05 |
| 48 | 0.21 | 1.01 | 1.02 |
| 50 | 0.20 | 1.09 | 1.10 |

