

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SMA-MALE RETURN LOSS (dB)	N-MALE RETURN LOSS (dB)
10	0.01	47.88	49.85
100	0.09	43.30	47.67
200	0.16	45.90	38.92
300	0.21	41.59	35.77
400	0.25	35.11	34.56
500	0.29	31.74	35.43
1000	0.44	41.37	39.60
1500	0.58	32.69	29.08
2000	0.70	33.64	31.89
2500	0.79	38.58	40.76
3000	0.87	33.68	31.26
3500	0.95	37.56	34.29
4000	1.03	37.41	42.11
4500	1.12	29.51	36.52
5000	1.20	30.40	35.66
5500	1.27	33.34	33.81
6000	1.34	34.24	35.30
6500	1.41	29.49	31.82
7000	1.46	35.43	34.64
7500	1.51	34.82	28.52
8000	1.56	32.99	27.11
8500	1.61	34.14	28.40
9000	1.67	30.34	29.73
9500	1.73	27.25	26.10
10000	1.78	30.13	25.18
10500	1.83	37.66	24.45
11000	1.88	29.50	21.96
11500	1.93	25.57	20.18
12000	1.98	28.22	22.05
12500	2.02	39.59	28.31
13000	2.08	25.18	25.37
13500	2.15	22.51	22.90
14000	2.19	25.21	27.74
14500	2.22	29.05	27.34
15000	2.28	24.05	20.20
15500	2.34	22.54	18.61
16000	2.38	25.01	21.29
16500	2.42	29.20	28.96
17000	2.46	24.15	26.77
17500	2.51	23.37	26.41
18000	2.55	24.78	31.87