

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
100	98.77	0.15
500	91.91	0.35
1000	90.70	0.46
2000	84.55	0.44
3000	75.58	0.37
4000	68.86	0.53
5000	63.02	0.74
6000	56.79	0.90
7000	51.88	1.00
8000	48.61	1.04
9000	45.78	1.05
10000	41.98	1.10
10800	37.82	1.22
12000	30.23	1.60
13000	24.72	1.86
14000	20.04	1.87
15000	12.64	2.20
16000	2.46	9.59
17000	1.17	17.12
17200	1.12	18.83
17400	1.09	21.69
17600	1.07	25.34
17800	1.07	29.27
18000	1.08	31.84
18200	1.10	29.93
18400	1.14	25.80
18600	1.18	21.93
18800	1.22	19.13
19000	1.27	17.18
19200	1.31	15.96
19400	1.33	15.54
19600	1.33	15.80
19800	1.32	16.97
20000	1.31	19.02
20200	1.32	22.03
20400	1.37	24.61
20600	1.45	22.86
20800	1.58	19.73
21000	1.74	17.39
22000	5.03	7.14
23000	16.26	3.26
24000	26.81	2.62
25000	35.11	2.30
26000	42.47	2.31
27000	51.68	2.82
28000	65.37	3.29
29000	58.02	2.77
30000	54.37	2.16
31000	51.13	2.14
32000	46.81	2.74
33000	44.91	3.33
34000	43.14	3.17
35000	40.47	2.83
36000	39.24	2.68
37000	40.23	2.68
38000	40.82	2.92
39000	41.10	3.47
40000	42.71	3.64
41000	52.78	3.39
42000	38.55	3.37
43000	24.46	3.57
44000	8.04	9.05
45000	6.18	6.98
46000	5.44	8.40
47000	3.62	20.92
48000	6.34	7.45
49000	9.96	4.69
50000	11.24	4.77