

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
100	103.77	0.01
500	87.11	0.01
1000	80.83	0.04
2000	74.97	0.07
3000	71.27	0.13
4000	69.97	0.18
5000	68.97	0.10
6000	69.27	0.01
7000	70.56	0.09
8000	77.58	0.13
9000	75.03	0.01
10000	63.18	0.14
11000	56.04	0.18
12000	49.80	0.16
13000	44.55	0.04
14000	42.10	0.27
15000	40.78	0.40
16000	11.58	1.62
17000	1.26	19.36
17700	0.98	22.97
18000	0.98	16.37
18200	1.01	15.30
18400	1.02	14.73
18600	0.99	15.75
18800	0.98	16.75
19000	0.95	19.50
19200	0.94	22.19
19400	0.97	21.76
19600	0.99	20.75
19800	1.04	19.83
20000	1.09	19.68
20200	1.13	21.84
21000	1.66	20.40
22000	12.19	1.50
23000	35.80	0.41
24000	49.41	0.58
25000	50.75	0.62
26000	63.35	0.51
27000	57.73	0.45
28000	52.33	0.40
29000	50.01	0.10
30000	49.45	0.01
31000	50.56	0.14
32000	54.28	0.21
33000	56.26	0.40
34000	53.98	0.35
35000	51.43	0.27
36000	49.10	0.05
37000	47.41	0.31
38000	46.29	0.31
39000	45.31	0.05
40000	43.60	2.06