

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	N-FEMALE VSWR (:1)	N-MALE VSWR (:1)
50	0.01	1.11	1.11
100	0.00	1.05	1.06
200	0.01	1.01	1.03
300	0.01	1.01	1.02
400	0.02	1.01	1.01
500	0.02	1.02	1.01
600	0.02	1.02	1.01
700	0.02	1.02	1.01
800	0.03	1.02	1.01
1000	0.04	1.02	1.01
1500	0.06	1.02	1.02
2000	0.08	1.03	1.03
2500	0.08	1.04	1.04
3000	0.09	1.06	1.06
3500	0.12	1.08	1.08
4000	0.14	1.11	1.10
4500	0.15	1.12	1.13
5000	0.17	1.13	1.15
5500	0.19	1.13	1.17
6000	0.19	1.12	1.18
6500	0.20	1.11	1.19
7000	0.21	1.11	1.19
7500	0.23	1.11	1.18
8000	0.25	1.11	1.17
8500	0.27	1.12	1.16
9000	0.28	1.11	1.14
9500	0.29	1.11	1.10
10000	0.27	1.08	1.07
10500	0.27	1.04	1.05
11000	0.26	1.06	1.05
11500	0.27	1.12	1.07
12000	0.29	1.18	1.11
12500	0.31	1.23	1.14
13000	0.33	1.24	1.16
13500	0.35	1.21	1.18
14000	0.37	1.19	1.16
15000	0.37	1.14	1.11
16000	0.35	1.06	1.15
17000	0.41	1.06	1.07
18000	0.51	1.07	1.18