

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.92mm-MALE 1 RETURN LOSS (dB)	2.92mm-MALE 2 RETURN LOSS (dB)
100	0.21	47.6	46.4
1000	0.66	57.0	53.8
2000	0.92	40.3	37.5
3000	1.11	42.6	48.1
4000	1.28	50.6	37.9
5000	1.43	32.2	32.0
6000	1.57	38.1	40.4
7000	1.71	25.8	26.8
8000	1.81	35.2	34.3
9000	1.95	23.5	23.6
10000	2.03	29.9	32.7
11000	2.15	25.6	26.0
12000	2.24	30.4	38.9
13000	2.35	23.8	24.0
14000	2.42	32.4	37.0
15000	2.52	26.2	27.8
16000	2.60	32.1	43.6
17000	2.71	23.9	25.3
18000	2.78	39.4	36.6
19000	2.90	23.3	24.7
20000	2.95	32.0	37.2
21000	3.02	32.9	34.4
22000	3.09	43.7	35.5
23000	3.18	31.2	33.0
24000	3.30	30.6	29.2
25000	3.39	32.5	30.6
26000	3.47	27.3	27.0
27000	3.54	30.4	26.5
28000	3.64	22.9	22.1
29000	3.69	35.9	28.4
30000	3.78	22.5	22.1
31000	3.84	30.4	31.6
32000	3.93	23.8	21.5
33000	3.99	33.0	25.6
34000	4.07	24.0	23.2
35000	4.14	33.9	26.3
36000	4.21	25.8	24.1
37000	4.27	29.2	29.4
38000	4.35	26.2	25.4
39000	4.43	25.2	29.1
40000	4.50	23.8	24.6