

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.4mm-MALE 1 RETURN LOSS (dB)	2.4mm-MALE 2 RETURN LOSS (dB)
100	0.13	40.6	41.1
1000	0.43	38.9	40.6
2000	0.59	42.9	37.5
4000	0.84	40.1	38.0
6000	1.04	35.0	34.9
8000	1.21	40.5	36.5
10000	1.36	44.0	49.3
12000	1.50	35.3	32.5
14000	1.63	39.5	39.1
16000	1.75	38.8	39.2
18000	1.86	37.7	36.6
20000	1.98	27.1	27.9
21500	2.06	36.5	42.8
22500	2.12	37.6	32.5
23500	2.17	43.0	41.7
24500	2.23	33.6	43.9
25500	2.29	28.3	31.7
26500	2.36	27.0	27.4
27500	2.40	34.9	34.6
28500	2.45	33.0	32.7
30000	2.53	36.1	34.1
31000	2.58	33.4	40.0
32000	2.63	35.3	43.0
33000	2.68	35.8	39.4
34000	2.73	40.8	38.6
35000	2.78	31.4	31.8
36000	2.83	33.1	32.0
37000	2.88	32.1	31.1
38000	2.92	35.2	31.2
39000	2.97	34.5	31.4
40000	3.02	37.4	33.2
41000	3.06	43.2	30.9
42000	3.10	38.8	34.6
43000	3.15	46.3	33.6
44000	3.18	36.0	33.5
45000	3.24	35.2	40.8
46000	3.29	38.5	37.1
47000	3.34	32.3	32.8
48000	3.39	41.1	35.1
49000	3.43	31.4	30.4
50000	3.49	30.2	29.5