

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	1.85mm-MALE 1 RETURN LOSS (dB)	1.85mm-MALE 2 RETURN LOSS (dB)
50	0.13	38.74	39.39
100	0.19	43.79	48.76
500	0.42	47.94	58.17
1000	0.59	42.37	41.93
2000	0.84	45.88	40.77
3000	1.03	46.75	42.67
4000	1.19	38.24	38.20
5000	1.34	35.95	44.44
6000	1.48	34.11	34.09
7000	1.61	29.98	29.97
8000	1.72	31.16	31.60
9000	1.83	35.17	34.03
10000	1.94	32.14	33.23
11000	2.04	36.25	35.38
12000	2.14	28.59	31.53
13000	2.24	28.22	28.86
14000	2.32	31.80	33.68
15000	2.41	37.04	34.74
16000	2.50	32.19	32.01
17000	2.58	31.79	36.89
18000	2.66	38.08	45.75
19000	2.75	30.95	35.17
20000	2.83	34.00	36.72
21000	2.90	32.89	37.11
22000	2.99	29.90	28.26
23000	3.06	34.20	34.96
24000	3.13	39.79	39.74
25000	3.21	39.67	38.48
26000	3.29	30.64	27.67
26500	3.32	39.00	31.00
27000	3.35	37.71	30.79
28000	3.42	39.03	29.04
30000	3.57	35.17	29.79
32000	3.70	36.48	30.04
34000	3.84	35.41	29.11
36000	3.97	39.27	28.51
38000	4.10	35.46	30.01
40000	4.23	42.84	31.81
42000	4.36	59.07	34.56
44000	4.50	31.67	31.02
46000	4.63	25.58	27.54
48000	4.75	30.67	28.06
50000	4.86	27.59	27.21
52000	4.98	28.04	30.33
54000	5.11	26.06	33.04
56000	5.23	26.67	27.49
58000	5.35	30.31	27.28
60000	5.50	28.32	33.21
62000	5.62	29.32	35.66
64000	5.75	26.59	39.07
66000	5.91	26.19	29.32
67000	5.90	20.87	19.68