

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.92mm-MALE 1 RETURN LOSS (dB)	2.92mm-MALE 2 RETURN LOSS (dB)
100	0.12	38.07	37.71
200	0.18	36.53	37.02
300	0.23	36.44	36.37
500	0.30	42.55	42.38
600	0.33	35.64	35.62
800	0.37	35.02	35.01
1000	0.42	32.87	32.93
2500	0.65	29.96	29.34
4000	0.82	33.09	31.25
5500	0.95	49.57	36.78
7000	1.07	37.04	37.83
8500	1.18	34.85	34.80
10000	1.28	32.41	30.73
11500	1.38	28.66	27.08
13000	1.47	32.49	29.23
14500	1.55	39.06	30.73
16000	1.63	36.67	29.30
17500	1.72	32.02	28.28
19000	1.81	26.54	24.56
20500	1.89	26.71	23.91
22000	1.95	30.59	24.49
23500	2.03	29.04	23.64
25000	2.11	27.00	23.32
26500	2.20	21.95	20.41
28000	2.26	24.09	22.38
29500	2.30	38.98	26.03
31000	2.37	29.97	25.42
32500	2.43	29.91	26.70
34000	2.50	30.21	29.01
35500	2.56	27.66	28.78
37000	2.62	28.30	29.90
38500	2.67	34.31	34.15
40000	2.74	38.19	38.55