

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SSMP-FEMALE RETURN LOSS (dB)	2.4mm-MALE RETURN LOSS (dB)
100	0.16	37.66	37.30
200	0.21	36.89	36.67
300	0.26	36.25	36.81
500	0.34	37.45	40.52
600	0.37	33.60	34.36
800	0.42	33.76	41.56
1000	0.47	30.14	31.85
2000	0.64	38.01	37.42
3000	0.77	31.97	31.12
4000	0.87	30.94	30.68
5000	0.96	37.62	39.18
6000	1.05	32.29	29.19
7000	1.14	23.54	22.30
8000	1.22	21.15	23.23
9000	1.28	21.43	32.00
10000	1.34	23.37	28.21
11000	1.39	29.51	27.84
12000	1.44	33.80	43.98
13000	1.51	26.30	25.15
14000	1.57	24.89	22.67
15000	1.62	26.49	27.09
16000	1.67	26.82	30.79
17000	1.71	29.83	24.38
18000	1.75	38.28	24.46
19000	1.81	31.34	29.54
20000	1.89	25.77	24.12
21000	1.95	24.48	23.09
22000	1.99	25.45	27.20
23000	2.03	25.08	25.73
24000	2.09	24.65	21.98
25000	2.15	23.20	21.96
26000	2.19	25.06	28.55
27000	2.22	26.84	44.39
28000	2.26	34.31	35.57
29000	2.31	37.33	43.74
30000	2.37	29.00	28.92
31000	2.41	28.08	22.96
32000	2.45	32.40	24.96
33000	2.49	33.94	25.66
34000	2.55	29.65	25.32
35000	2.59	33.62	29.16
36000	2.62	32.67	21.93
37000	2.67	26.89	21.39
38000	2.73	24.90	26.08
39000	2.83	19.70	20.64
40000	2.87	19.62	19.67