

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.4mm-MALE 1 RETURN LOSS (dB)	2.4mm-MALE 2 RETURN LOSS (dB)
100	0.12	37.86	38.27
200	0.19	36.81	37.49
400	0.27	36.89	36.58
600	0.34	33.81	34.17
800	0.39	34.96	35.17
1000	0.45	30.99	31.10
2000	0.62	43.65	42.18
3500	0.82	38.47	36.58
5000	0.97	40.98	34.97
6500	1.09	37.26	34.77
8000	1.21	41.97	43.49
9500	1.31	33.23	33.90
11000	1.41	30.23	30.39
12500	1.50	31.52	31.47
14000	1.58	38.85	39.09
15500	1.66	33.49	33.50
17000	1.75	29.84	31.65
18500	1.83	29.30	30.52
20000	1.90	35.46	38.48
21500	1.99	37.62	39.79
23000	2.06	43.26	34.13
24500	2.14	34.54	29.29
26000	2.22	30.43	28.40
27500	2.30	24.75	25.34
29000	2.37	25.69	28.20
30500	2.44	32.11	38.00
32000	2.51	30.00	35.78
33500	2.58	30.58	35.24
35000	2.64	34.84	48.73
36500	2.72	29.02	31.57
38000	2.80	25.64	24.66
39500	2.87	33.29	28.05
41000	2.95	26.65	22.25
42500	3.03	22.81	20.86
44000	3.09	20.79	20.00
45500	3.15	20.44	21.00
47000	3.20	23.44	25.23
48500	3.25	27.74	39.37
50000	3.24	34.19	36.02