

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SSMP-FEMALE RETURN LOSS (dB)	2.92mm-MALE RETURN LOSS (dB)
100	0.09	37.26	37.52
200	0.13	35.28	35.48
300	0.16	36.05	36.60
400	0.19	40.11	40.79
500	0.21	46.03	46.44
600	0.23	38.97	39.45
700	0.24	34.06	35.25
800	0.26	32.04	33.95
900	0.27	31.77	34.25
1000	0.28	33.37	37.23
2000	0.38	40.03	40.66
3000	0.45	27.95	32.31
4000	0.51	26.20	29.17
5000	0.57	24.40	23.71
6000	0.61	27.50	26.27
7000	0.65	24.41	26.46
8000	0.69	25.48	26.64
9000	0.75	21.04	21.12
10000	0.77	24.47	23.65
11000	0.78	33.49	35.91
12000	0.82	27.21	24.46
13000	0.88	20.67	20.16
14000	0.87	26.53	29.85
15000	0.91	23.63	22.94
16000	0.95	23.78	21.71
17000	0.96	28.40	29.70
18000	1.03	21.13	19.26
19000	1.03	26.96	25.51
20000	1.05	30.62	26.97
21000	1.08	25.58	24.71
22000	1.10	31.39	33.62
23000	1.13	30.37	26.25
24000	1.17	22.15	22.42
25000	1.18	31.46	28.42
26000	1.21	27.19	24.67
27000	1.24	30.58	27.05
28000	1.27	29.78	27.36
29000	1.31	23.69	25.37
30000	1.35	26.05	22.97
31000	1.36	24.09	45.07
32000	1.41	23.06	24.33
33000	1.42	27.62	20.74
34000	1.51	18.88	21.07
35000	1.49	25.01	26.06
36000	1.54	19.85	18.41
37000	1.54	19.77	21.22
38000	1.51	25.32	31.06
39000	1.54	20.29	22.40
40000	1.57	21.65	20.63