

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	SSMP-FEMALE RETURN LOSS (dB)	2.4mm-MALE RETURN LOSS (dB)
100	0.07	37.00	37.14
200	0.11	35.09	35.39
300	0.14	35.78	36.62
400	0.16	39.30	42.10
500	0.18	43.58	49.25
600	0.20	37.91	39.07
700	0.21	33.74	35.05
800	0.23	31.79	33.46
900	0.24	31.19	33.67
1000	0.25	32.19	36.83
2000	0.33	35.96	34.14
3000	0.42	30.88	29.69
4000	0.48	27.50	28.01
5000	0.54	24.11	22.71
6000	0.56	29.90	26.79
7000	0.61	23.61	28.58
8000	0.65	22.83	21.27
9000	0.67	27.27	23.54
10000	0.72	22.83	32.33
11000	0.73	33.25	29.51
12000	0.77	30.07	28.93
13000	0.80	28.83	25.00
14000	0.84	22.95	24.29
15000	0.86	25.94	31.54
16000	0.90	21.55	24.29
17000	0.91	25.63	20.90
18000	0.96	20.52	22.31
19000	0.98	24.70	36.47
20000	1.02	23.10	20.62
21000	1.06	21.96	19.05
22000	1.04	34.90	23.06
23000	1.07	27.75	24.76
24000	1.10	26.48	20.52
25000	1.14	25.40	23.83
26000	1.16	28.93	33.23
27000	1.21	20.64	28.14
28000	1.23	23.03	28.42
29000	1.24	25.30	29.32
30000	1.28	24.75	21.56
31000	1.30	30.83	20.51
32000	1.31	43.53	26.19
33000	1.36	24.82	18.93
34000	1.39	26.63	24.95
35000	1.43	21.10	22.49
36000	1.44	22.35	19.06
37000	1.42	26.25	22.88
38000	1.45	24.35	33.17
39000	1.48	24.06	21.83
40000	1.49	25.20	24.74