

Test Cable, SMA-Male/SMA-Male

FLC-3FT-SMSM+

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	SMA-MALE 1 VSWR (:1)	SMA-MALE 2 VSWR (:1)
0.1	0.16	1.01	1.02
0.5	0.29	1.03	1.03
1.0	0.39	1.05	1.05
1.5	0.48	1.06	1.06
2.0	0.55	1.07	1.07
2.5	0.63	1.07	1.08
3.0	0.70	1.07	1.07
3.5	0.75	1.07	1.06
4.0	0.80	1.06	1.05
4.5	0.84	1.06	1.04
5.0	0.89	1.06	1.04
5.5	0.95	1.06	1.05
6.0	1.00	1.08	1.08
6.5	1.04	1.10	1.09
7.0	1.10	1.11	1.08
7.5	1.16	1.13	1.10
8.0	1.20	1.16	1.13
8.5	1.21	1.18	1.15
9.0	1.24	1.18	1.15
9.5	1.27	1.17	1.14
10.0	1.29	1.16	1.13
10.5	1.29	1.16	1.15
11.0	1.38	1.17	1.15
11.5	1.38	1.16	1.14
12.0	1.40	1.13	1.13
12.5	1.46	1.11	1.11
13.0	1.52	1.10	1.11
13.5	1.56	1.11	1.11
14.0	1.59	1.10	1.11
14.5	1.64	1.11	1.11
15.0	1.75	1.11	1.11
15.5	1.75	1.12	1.12
16.0	1.80	1.14	1.14
16.5	1.93	1.14	1.13
17.0	1.89	1.14	1.14
17.5	1.88	1.16	1.18
18.0	2.02	1.19	1.22
18.5	2.09	1.19	1.22
19.0	2.09	1.21	1.23
19.5	2.08	1.19	1.19
20.0	2.11	1.19	1.18
20.5	2.15	1.22	1.22
21.0	2.09	1.23	1.22
21.5	1.97	1.22	1.21
22.0	2.07	1.18	1.18
22.5	2.12	1.17	1.19
23.0	2.12	1.17	1.19
23.5	2.09	1.16	1.18
24.0	2.22	1.14	1.16
24.5	2.28	1.13	1.14
25.0	2.26	1.14	1.16
25.5	2.22	1.14	1.16
26.0	2.29	1.14	1.15

