

Termination 50 Ω , N-TYPE

KARN-50CN+

Typical Performance Data

FREQUENCY (MHz)	RETURN LOSS (dB)
100	46.31
600	46.36
1000	44.26
2000	39.83
3000	37.27
4000	35.14
5000	33.72
6000	34.35
7000	34.72
8000	34.96