

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
0.01	0.15	29.63	29.66
0.1	0.49	44.09	35.54
0.2	0.68	35.54	39.88
0.4	0.95	42.79	46.94
0.6	1.17	43.15	42.25
0.8	1.35	42.25	44.81
1.0	1.51	37.19	37.22
1.5	1.86	32.84	33.87
2.0	2.16	35.56	38.02
2.5	2.42	27.40	27.68
3.0	2.67	23.38	22.88
3.5	2.87	24.61	23.91
4.0	3.06	32.14	29.63
4.5	3.25	44.71	34.36
5.0	3.43	47.53	40.02
5.5	3.59	33.19	33.44
6.0	3.75	30.55	30.40
6.5	3.93	28.90	27.94
7.0	4.13	22.60	22.23
7.5	4.29	20.60	20.33
8.0	4.39	23.84	23.14
8.5	4.50	31.29	30.76
9.0	4.64	32.64	32.13
9.5	4.79	32.12	44.19
10.0	4.94	27.07	28.98
10.5	5.09	22.14	22.68
11.0	5.22	21.88	22.88
11.5	5.33	23.47	24.50
12.0	5.41	23.24	24.78
12.5	5.51	21.83	23.01
13.0	5.63	24.69	26.69
13.5	5.78	27.83	52.67
14.0	5.92	22.64	27.68
14.5	6.05	21.68	27.16
15.0	6.19	20.23	24.41
15.5	6.33	18.01	20.15
16.0	6.42	17.62	19.01
16.5	6.50	18.65	20.30
17.0	6.58	22.63	25.24
17.5	6.69	25.37	29.57
18.0	6.77	28.27	35.46

