

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.4mm-FEMALE RETURN LOSS (dB)	2.4mm-MALE RETURN LOSS (dB)
100	0.10	36.8	46.7
400	0.21	50.2	36.2
700	0.27	60.7	44.3
1000	0.32	42.1	43.4
1500	0.38	46.3	37.8
2000	0.44	36.6	36.5
2500	0.49	35.8	34.9
3000	0.53	47.4	38.6
3500	0.58	33.7	39.4
4000	0.61	31.0	32.0
4500	0.65	33.2	32.7
5000	0.68	36.5	38.6
5500	0.71	29.1	30.6
6000	0.74	30.0	29.9
6500	0.76	38.2	35.5
7000	0.79	35.1	34.9
7500	0.82	28.1	27.9
8000	0.85	28.6	28.2
9000	0.89	29.5	30.4
10000	0.93	31.7	31.8
11000	0.98	30.0	29.6
12000	1.01	39.7	38.9
13000	1.05	33.9	31.9
14000	1.09	38.6	39.8
15000	1.13	34.1	34.0
16000	1.16	41.5	45.9
17000	1.20	33.2	35.3
18000	1.24	39.8	40.5
20000	1.32	34.0	32.2
22000	1.40	24.9	26.4
24000	1.48	23.8	24.0
26000	1.54	25.1	22.7
28000	1.61	24.8	24.2
30000	1.66	24.8	26.4
32000	1.72	26.3	29.1
34000	1.78	26.5	28.5
36000	1.84	28.3	28.8
38000	1.90	34.5	28.5
40000	1.96	44.1	28.3