

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.92mm-MALE 1 RETURN LOSS (dB)	2.92mm-MALE 2 RETURN LOSS (dB)
100	0.14	46.1	40.1
400	0.28	36.4	38.1
700	0.37	39.9	39.3
1000	0.45	35.3	37.9
1500	0.55	31.1	34.9
2000	0.63	42.9	44.3
2500	0.70	44.3	46.7
3000	0.77	34.3	35.3
3500	0.83	38.2	37.2
4000	0.88	48.9	49.4
4500	0.94	39.8	43.1
5000	0.99	36.2	32.1
5500	1.03	32.4	32.7
6000	1.08	33.4	31.6
6500	1.12	29.2	31.9
7000	1.16	32.5	33.5
7500	1.20	30.2	30.4
8000	1.24	28.8	29.1
9000	1.31	29.7	29.9
10000	1.39	27.2	27.6
11000	1.46	27.2	26.5
12000	1.52	34.1	35.9
13000	1.58	32.2	33.5
14000	1.64	31.5	33.2
15000	1.70	30.2	30.2
16000	1.76	35.5	36.4
17000	1.82	38.8	36.8
18000	1.88	36.0	34.5
20000	1.99	39.5	38.7
22000	2.07	41.4	39.6
24000	2.22	29.8	29.7
26000	2.33	30.0	34.7
28000	2.41	34.1	42.0
30000	2.50	31.4	35.9
32000	2.60	27.5	30.9
34000	2.69	27.8	33.1
36000	2.78	25.9	30.2
38000	2.87	28.2	30.1
40000	2.96	30.7	29.5