

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.4mm-FEMALE RETURN LOSS (dB)	2.4mm-MALE RETURN LOSS (dB)
100	0.16	70.6	45.8
1000	0.48	39.6	37.2
3000	0.81	38.1	42.6
4000	0.92	35.8	38.2
5000	1.03	29.8	32.4
6000	1.12	29.2	29.8
7000	1.20	28.6	29.0
8000	1.28	31.0	32.6
9000	1.35	50.8	44.1
10000	1.42	29.1	30.0
11000	1.49	32.5	33.6
12000	1.55	28.6	29.4
13000	1.61	39.9	34.8
14000	1.67	36.7	38.7
15000	1.73	44.3	42.3
16000	1.79	43.1	42.4
17000	1.84	34.4	32.8
18000	1.90	33.6	30.6
19000	1.97	26.8	25.2
20000	2.02	27.9	25.4
21000	2.08	26.6	25.8
22000	2.13	34.1	29.9
23000	2.18	28.0	25.8
24000	2.26	23.2	22.1
25000	2.33	20.0	19.4
26000	2.37	21.6	19.4
27000	2.40	23.2	21.6
28000	2.44	27.7	24.5
29000	2.48	34.3	29.7
30000	2.53	28.8	26.9
31000	2.58	24.8	23.7
32000	2.63	23.2	22.7
33000	2.67	23.4	23.8
34000	2.71	26.2	26.0
35000	2.75	28.7	28.9
36000	2.79	32.4	36.6
37000	2.84	35.9	43.1
38000	2.88	30.3	36.9
39000	2.93	30.5	36.7
40000	2.97	29.6	38.3