

# RF Transformer

# TC4-25G2+

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
400	1.66	6.09
500	1.07	8.37
600	0.74	10.92
700	0.54	13.81
800	0.42	17.29
900	0.38	21.02
1000	0.37	22.67
1100	0.40	20.79
1200	0.43	18.40
1300	0.48	16.41
1400	0.53	14.94
1500	0.59	13.79
1600	0.64	12.90
1800	0.74	11.65
2000	0.84	10.75
2200	0.96	10.03
2400	1.08	9.35
2500	1.14	8.96
2800	1.38	7.82
3000	1.59	7.06