

*Typical Performance Data*

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.92mm-MALE 1 RETURN LOSS (dB)	2.92mm-MALE 2 RETURN LOSS (dB)
10	0.08	45.6	47.6
40	0.11	41.6	39.8
70	0.10	41.8	38.3
100	0.13	48.8	40.9
150	0.16	40.2	42.5
290	0.22	40.6	46.3
430	0.26	37.7	38.9
570	0.30	36.3	36.3
710	0.33	39.5	39.6
850	0.36	43.3	40.7
1000	0.39	45.5	47.9
1050	0.40	37.8	40.2
1870	0.53	34.9	35.1
2700	0.64	41.9	53.4
3520	0.73	30.6	30.3
4350	0.81	39.3	38.9
5170	0.88	31.3	31.1
6000	0.95	32.3	31.9
6050	0.95	32.9	33.0
6700	1.00	30.3	30.4
7360	1.05	26.8	26.9
8020	1.10	26.3	26.2
8680	1.14	26.6	26.5
9340	1.18	29.6	29.9
10000	1.22	35.0	36.1
10100	1.23	27.4	27.4
11410	1.30	34.0	33.0
12730	1.37	36.3	34.8
14050	1.45	26.4	25.8
15360	1.50	34.7	35.3
16680	1.57	30.8	32.2
18000	1.64	37.5	36.4
18200	1.65	31.8	36.9
20920	1.76	31.3	40.3
23650	1.92	21.8	22.1
26370	2.07	20.5	20.1
29100	2.15	25.3	23.3
31820	2.23	29.5	30.9
34550	2.33	26.7	36.7
37270	2.43	30.4	37.0
40000	2.53	26.2	28.4