

Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	2.92mm-MALE 1 RETURN LOSS (dB)	2.92mm-MALE 2 RETURN LOSS (dB)
100	0.11	42.5	41.6
1000	0.36	42.7	63.3
2000	0.52	43.3	41.7
3000	0.62	37.4	37.2
4000	0.73	32.5	31.6
5000	0.81	30.1	30.2
6000	0.89	29.1	29.3
7000	0.96	30.7	30.6
8000	1.01	36.1	35.9
9000	1.07	43.9	38.6
10000	1.12	34.4	33.4
11000	1.18	33.0	32.7
12000	1.23	33.2	32.7
13000	1.28	33.3	33.1
14000	1.33	30.8	30.2
15000	1.37	44.4	39.1
16000	1.42	36.6	38.3
17000	1.46	37.2	35.4
18000	1.51	47.2	48.0
19000	1.57	26.4	25.7
20000	1.60	30.7	29.5
21000	1.62	29.7	29.7
22000	1.66	26.5	25.3
23000	1.70	31.0	27.8
24000	1.78	31.0	28.0
25000	1.82	34.4	29.5
26000	1.86	34.8	28.1
27000	1.89	36.5	30.3
28000	1.93	30.3	28.3
29000	1.96	28.1	27.3
30000	1.99	28.5	29.8
31000	2.04	24.5	26.6
32000	2.07	27.8	30.7
33000	2.12	23.6	25.9
34000	2.17	20.2	21.9
35000	2.20	21.5	22.1
36000	2.22	23.5	24.3
37000	2.24	26.7	25.6
38000	2.28	25.3	30.9
39000	2.30	34.8	29.1
40000	2.34	27.2	25.1