

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	N-MALE RETURN LOSS (dB)	SMA-MALE RETURN LOSS (dB)
0.01	0.05	40.88	40.50
0.1	0.17	60.70	59.79
0.2	0.24	47.85	48.13
0.4	0.34	52.05	46.25
0.6	0.43	42.24	39.38
0.8	0.49	40.98	38.27
1.0	0.55	32.08	31.51
1.5	0.69	27.98	28.08
2.0	0.80	34.32	38.57
2.5	0.91	25.44	25.42
3.0	1.00	28.94	28.89
3.5	1.08	31.58	32.07
4.0	1.16	27.85	27.30
4.5	1.24	28.69	28.30
5.0	1.31	33.43	33.09
5.5	1.38	32.57	30.89
6.0	1.45	38.75	34.48
6.5	1.51	35.59	35.33
7.0	1.58	34.43	31.38
7.5	1.64	32.86	33.77
8.0	1.71	31.25	31.19
8.5	1.77	40.44	38.20
9.0	1.83	27.17	29.52
9.5	1.89	30.52	30.93
10.0	1.95	37.44	32.18
10.5	2.01	26.75	27.45
11.0	2.06	31.83	28.07
11.5	2.12	31.91	26.58
12.0	2.18	26.12	23.01
12.5	2.23	32.07	25.74
13.0	2.28	30.34	25.00
13.5	2.34	29.19	22.55
14.0	2.38	38.15	26.86
14.5	2.45	28.41	22.82
15.0	2.49	31.95	22.01
15.5	2.53	31.86	27.61
16.0	2.60	25.21	20.77
16.5	2.64	29.60	22.19
17.0	2.69	26.26	26.29
17.5	2.77	21.48	19.50
18.0	2.79	28.43	22.98