

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
0.01	0.03	42.32	42.84
0.05	0.08	33.91	33.77
0.1	0.11	34.79	34.43
0.5	0.25	37.22	37.16
1.0	0.36	34.26	34.31
1.5	0.44	41.01	41.21
2.0	0.51	27.31	27.37
2.5	0.59	22.42	22.47
3.0	0.65	23.08	23.21
3.5	0.70	24.82	24.86
4.0	0.74	37.46	36.82
4.5	0.79	36.15	36.88
5.0	0.83	31.27	30.26
5.5	0.88	32.45	30.18
6.0	0.92	47.75	38.05
6.5	0.96	36.70	45.12
7.0	1.01	30.09	32.59
7.5	1.05	28.76	30.53
8.0	1.09	27.39	28.12
8.5	1.12	29.10	30.02
9.0	1.16	29.09	29.57
9.5	1.19	31.35	32.93
10.0	1.23	34.51	52.77
10.5	1.27	28.26	30.03
11.0	1.32	22.52	23.09
11.5	1.39	18.92	19.16
12.0	1.41	20.01	20.96
12.5	1.43	21.68	22.85
13.0	1.45	26.95	27.28
13.5	1.47	34.34	31.50
14.0	1.50	42.44	31.87
14.5	1.53	33.98	35.94
15.0	1.56	28.65	30.90
15.5	1.59	27.18	27.53
16.0	1.63	26.96	25.03
16.5	1.68	27.94	23.65
17.0	1.71	27.63	23.33
17.5	1.74	27.53	25.02
18.0	1.76	26.59	28.01

