

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	N-MALE RETURN LOSS (dB)	SMA-MALE RETURN LOSS (dB)
0.01	0.04	39.12	39.14
0.1	0.15	40.22	39.31
0.2	0.21	36.29	36.11
0.4	0.31	31.74	31.56
0.6	0.38	32.42	31.75
0.8	0.45	35.61	36.42
1.0	0.50	32.47	32.77
1.5	0.62	34.04	35.53
2.0	0.73	26.44	26.45
2.5	0.82	24.50	24.49
3.0	0.90	29.05	29.60
3.5	0.97	42.95	43.08
4.0	1.05	31.72	30.21
4.5	1.12	29.96	28.71
5.0	1.18	31.30	30.29
5.5	1.24	40.01	33.37
6.0	1.30	33.63	29.62
6.5	1.37	27.65	25.76
7.0	1.43	27.62	27.01
7.5	1.48	29.06	30.00
8.0	1.54	41.65	31.70
8.5	1.60	27.55	25.15
9.0	1.66	23.66	23.82
9.5	1.71	23.62	24.50
10.0	1.75	30.91	30.26
10.5	1.81	31.70	27.29
11.0	1.87	23.90	23.16
11.5	1.93	23.44	22.23
12.0	1.96	30.44	25.53
12.5	2.00	31.85	27.63
13.0	2.06	26.12	23.59
13.5	2.10	27.41	22.55
14.0	2.14	34.32	25.89
14.5	2.19	36.96	32.57
15.0	2.23	33.43	28.44
15.5	2.28	29.98	22.70
16.0	2.32	27.39	21.80
16.5	2.37	26.17	24.85
17.0	2.41	27.50	30.50
17.5	2.46	29.37	24.79
18.0	2.52	21.96	19.63

