

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
0.01	0.05	38.82	38.60
0.05	0.12	32.89	32.44
0.1	0.16	45.21	43.77
0.5	0.37	35.72	35.54
1.0	0.53	39.81	39.70
1.5	0.65	27.28	27.52
2.0	0.75	28.42	28.86
2.5	0.84	36.75	48.13
3.0	0.94	25.97	26.57
3.5	1.02	26.43	27.37
4.0	1.09	31.11	38.53
4.5	1.16	28.89	31.15
5.0	1.23	32.72	35.04
5.5	1.30	29.91	31.21
6.0	1.37	32.71	31.44
6.5	1.43	30.46	29.62
7.0	1.49	29.05	27.56
7.5	1.57	23.18	22.93
8.0	1.61	28.30	26.36
8.5	1.68	25.31	24.19
9.0	1.77	19.99	19.68
9.5	1.79	30.98	25.50
10.0	1.86	22.04	20.82
10.5	1.94	19.37	18.77
11.0	1.94	33.18	25.12
11.5	2.03	20.60	19.52
12.0	2.08	19.31	18.73
12.5	2.08	30.08	26.12
13.0	2.16	21.88	19.61
13.5	2.19	21.91	20.94
14.0	2.22	31.64	26.09
14.5	2.28	32.32	21.76
15.0	2.33	29.38	25.35
15.5	2.36	29.73	25.80
16.0	2.42	31.12	21.92
16.5	2.48	29.00	22.97
17.0	2.51	25.79	23.48
17.5	2.58	25.75	19.25
18.0	2.63	25.05	19.85