

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	N-MALE RETURN LOSS (dB)	SMA-MALE RETURN LOSS (dB)
0.01	0.07	34.10	33.42
0.1	0.21	34.96	35.01
0.2	0.29	31.97	31.54
0.4	0.42	32.11	32.07
0.6	0.52	43.91	42.89
0.8	0.61	29.41	28.70
1.0	0.68	30.22	29.83
1.5	0.85	27.47	25.92
2.0	0.98	30.91	31.61
2.5	1.10	30.22	30.67
3.0	1.23	23.78	23.98
3.5	1.33	26.29	29.08
4.0	1.42	34.14	30.75
4.5	1.53	28.59	27.93
5.0	1.61	29.22	30.45
5.5	1.70	37.89	30.83
6.0	1.79	30.83	26.99
6.5	1.87	31.69	26.82
7.0	1.95	33.41	29.35
7.5	2.04	26.77	24.59
8.0	2.11	34.03	25.49
8.5	2.18	27.60	26.86
9.0	2.26	22.02	23.69
9.5	2.34	25.54	23.17
10.0	2.40	42.18	26.75
10.5	2.47	23.57	24.18
11.0	2.56	21.53	21.58
11.5	2.61	27.97	26.24
12.0	2.67	28.06	25.44
12.5	2.76	23.19	21.42
13.0	2.81	25.95	25.64
13.5	2.87	42.15	29.54
14.0	2.95	25.21	23.13
14.5	3.00	25.91	25.51
15.0	3.06	41.19	39.69
15.5	3.13	26.06	26.86
16.0	3.18	28.44	29.16
16.5	3.24	29.93	34.80
17.0	3.31	23.81	26.86
17.5	3.36	25.94	31.56
18.0	3.41	26.50	31.67