

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
0.01	0.06	37.75	37.84
0.05	0.14	33.74	33.63
0.1	0.20	37.60	36.87
0.5	0.47	51.27	51.80
1.0	0.68	46.44	45.53
1.5	0.84	28.58	28.86
2.0	0.98	25.59	25.92
2.5	1.10	28.93	29.61
3.0	1.21	31.63	33.28
3.5	1.33	24.97	25.18
4.0	1.42	26.74	27.04
4.5	1.51	34.11	46.12
5.0	1.60	29.02	31.01
5.5	1.69	27.81	28.85
6.0	1.77	39.27	37.19
6.5	1.85	32.66	31.57
7.0	1.94	27.74	28.29
7.5	2.01	28.56	28.44
8.0	2.08	37.99	31.13
8.5	2.17	26.87	26.81
9.0	2.25	24.78	24.72
9.5	2.31	26.96	26.59
10.0	2.37	40.98	32.03
10.5	2.45	26.73	26.29
11.0	2.53	22.20	22.09
11.5	2.59	22.48	22.47
12.0	2.64	28.08	28.18
12.5	2.70	27.24	28.68
13.0	2.76	24.00	24.00
13.5	2.82	24.68	23.72
14.0	2.88	27.55	27.55
14.5	2.94	27.87	38.23
15.0	3.00	30.39	32.79
15.5	3.06	32.97	29.03
16.0	3.12	31.75	31.89
16.5	3.18	28.23	44.62
17.0	3.25	32.28	33.77
17.5	3.31	35.00	27.48
18.0	3.36	35.15	29.12