

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	N-MALE 1 RETURN LOSS (dB)	N-MALE 2 RETURN LOSS (dB)
0.01	0.16	35.05	34.78
0.1	0.30	39.37	38.70
0.2	0.44	39.09	38.60
0.4	0.64	36.00	35.67
0.6	0.79	35.95	33.86
0.8	0.92	30.60	30.65
1.0	1.03	28.58	28.40
1.5	1.29	26.77	26.34
2.0	1.50	24.96	24.25
2.5	1.69	25.41	24.42
3.0	1.86	26.11	24.05
3.5	2.02	27.18	25.50
4.0	2.16	29.30	26.49
4.5	2.31	27.77	26.67
5.0	2.44	29.04	32.16
5.5	2.56	29.66	33.62
6.0	2.69	28.36	33.21
6.5	2.80	28.40	34.06
7.0	2.91	28.41	34.09
7.5	3.02	28.51	34.93
8.0	3.13	27.98	35.16
8.5	3.23	28.03	36.49
9.0	3.34	29.21	37.90
9.5	3.46	28.32	37.99
10.0	3.58	30.58	37.25
10.5	3.70	31.99	42.13
11.0	3.81	32.75	42.66
11.5	3.91	35.29	34.82
12.0	4.01	35.89	32.58
12.5	4.10	34.23	29.10
13.0	4.19	34.05	30.04
13.5	4.27	33.07	31.02
14.0	4.38	30.76	30.33
14.5	4.49	29.87	30.50
15.0	4.61	30.15	28.89
15.5	4.71	29.34	28.33
16.0	4.80	29.22	30.70
16.5	4.87	28.08	32.41
17.0	4.99	26.63	32.44
17.5	5.09	26.06	33.19
18.0	5.21	26.88	32.15

