

Typical Performance Data

FREQUENCY (GHz)	INSERTION LOSS (dB)	SMA-MALE 1 RETURN LOSS (dB)	SMA-MALE 2 RETURN LOSS (dB)
0.1	0.40	39.00	40.75
0.2	0.57	52.14	47.36
0.3	0.70	37.81	38.27
0.4	0.81	44.23	45.40
0.5	0.91	44.40	46.63
0.6	1.00	34.90	34.70
0.7	1.08	34.70	34.36
0.8	1.16	38.81	39.15
0.9	1.23	30.35	30.16
1.0	1.30	29.92	29.60
1.5	1.61	30.35	29.57
2.0	1.89	33.67	32.38
2.5	2.12	26.24	25.69
3.0	2.40	23.95	23.68
3.5	2.58	25.25	24.90
4.0	2.70	31.23	30.56
4.5	2.88	26.27	26.28
5.0	3.07	36.06	34.39
5.5	3.25	33.17	31.50
6.0	3.42	27.44	27.01
6.5	3.57	29.00	29.76
7.0	3.74	27.95	27.76
7.5	3.87	28.19	34.22
8.0	4.04	28.88	28.26
8.5	4.19	33.79	27.74
9.0	4.30	24.80	29.56
9.5	4.46	30.35	28.12
10.0	4.58	28.12	25.14
10.5	4.70	29.45	27.12
11.0	4.91	27.89	26.51
11.5	4.96	27.82	24.97
12.0	4.99	26.55	24.09
12.5	5.20	27.07	26.77
13.0	5.26	27.07	24.51
13.5	5.44	26.54	26.30
14.0	5.62	26.25	25.98
14.5	5.60	28.86	25.43
15.0	5.80	26.61	26.11
15.5	6.01	27.84	25.12
16.0	5.99	25.60	24.13
16.5	6.19	29.22	25.52
17.0	6.27	28.04	26.49
17.5	6.36	24.76	24.43
18.0	6.55	24.28	24.37