

# Coaxial SMA Band Pass Filter

# VBFZ-2340-S+

## Typical Performance Data

FREQUENCY (MHz)	INSERTION LOSS (dB)	RETURN LOSS (dB)
50	79.11	0.18
500	75.05	0.04
1000	55.64	0.11
1400	35.23	0.52
1450	29.70	0.56
1514	23.17	0.82
1630	12.16	1.88
1700	6.35	4.55
1785	2.64	14.43
2020	1.39	19.10
2340	1.51	11.40
2660	1.79	10.26
3145	3.94	7.83
3315	8.89	3.81
3480	16.47	1.92
3800	32.80	0.82
3815	33.59	0.86
6000	35.17	0.57
8500	29.30	0.39
9000	24.43	0.62

REV. OR  
VBFZ-2340-S+  
200810  
Page 1 of 1



IF/RF MICROWAVE COMPONENTS • ISO 9001 ISO 14001 AS 9100 CERTIFIED RoHS compliant  
P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661



The Design Engineers Search Engine finds the model you need, Instantly • For detailed performance specs & shopping online see

