

*Typical Performance Data*

Test Condition @ Temperature = +25°C

FREQ. (MHz)	INSERTION LOSS (dB)	INPUT VSWR (:1)	OUTPUT VSWR (:1)
10	0.56	1.03	1.03
100	0.57	1.03	1.03
500	0.58	1.06	1.06
1000	0.62	1.10	1.10
2000	0.74	1.18	1.19
3000	0.90	1.24	1.26
4000	1.11	1.24	1.26
5000	1.36	1.18	1.19
6600	2.29	1.22	1.15
7100	3.00	1.29	1.22
8000	6.38	1.26	1.25
9200	26.04	1.36	1.20
10000	29.19	1.56	1.20
12000	27.60	1.54	1.19
16000	33.94	1.37	1.62
20000	37.11	1.75	1.85
30000	28.55	1.91	1.77
40000	51.28	1.27	1.02
43500	56.16	1.23	1.24